

CODICE PRODOTTO
DS3

Tecnologie
UV HD GH



SCATOLA DA 3
LENTI A CONTATTO

Disponibile in stock e
private label

HYDROSI 100-T

ONE | TORIC

TECHNICAL FILE

Materiale	Innofilcon A
Contenuto d'acqua	45%
Geometria	Asferica
Curva base	8.60 mm
Diametro	14.20 mm
Spessore centrale	0.093 mm (a -3.00 Dt)
Tinta Manipolazione	Leggermente azzurrata
Dk	88
Dk/t	95
Orientamento	Tracciamento a 270°
Modulo	0,8 Mpa
Cilindro	-0.75 - 1.25 -1.75 -2,25
Asse	da 10° a 180° (step di 10°)

CARATTERISTICHE DEL PRODOTTO

Realizzate con Tecnologia HD, ad alta definizione, per compensare le aberrazioni visive causate dall'applicazione della lente sull'occhio e offrire una visione più nitida e definita.

La superficie ottica asferica è prodotta con tecnologie di alta precisione per favorire una migliore interazione con la superficie corneale.

Elevata permeabilità all'ossigeno per favorire il corretto metabolismo corneale.

Lente immersa in soluzione salina tamponata con sodio ialuronato per miglior bagnabilità e lubrificazione, soprattutto nelle prime ore d'uso.

Modulo elastico 0,8 MPa: garantisce un buon equilibrio tra maneggevolezza e comfort, facilitando l'applicazione della lente.

Con filtro UV integrato nel materiale

GAMMA POTERI

-12.00 Dt ~ +6.00 Dt

da -12.00 a -6.50 (0.50 step)
da -6.00 a +6.00 (0.25 step)

**PRODUCT CODE
DS3**

Technologies

UV HD GH



**BOX WITH 3
CONTACT LENSES**

**Available in stock and
private label**

HYDROSI 100-T ONE | TORIC

TECHNICAL FILE

Material	Innofilcon A
Water content	45%
Geometry	Aspherical
Base curve	8.60 mm
Diameter	14.20 mm
Central thickness	0.093 mm (a -3.00 Dt)
Handling tint	Leggermente azzurrata
Dk	88
Dk/t	95
Orientation	Tracking at 270°
Module	0,8 Mpa
Cylinder	-0.75 - 1.25 -1.75 -2,25
Axis	from 10° to 180° (10°steps)

PRODUCT FEATURES

Made with HD technology, high definition, to compensate for visual aberrations caused by the application of the lens to the eye and offer sharper, more defined vision

The aspheric optical surface is produced with high-precision technologies to promote better interaction with the corneal surface

High oxygen permeability to promote proper corneal metabolism

Lens immersed in saline solution buffered with sodium hyaluronate for improved wettability and lubrication, especially in the first hours of use

Elastic modulus 0.8 MPa: ensures a good balance between handling and comfort, facilitating lens application

With UV filter integrated into the material

POWER RANGE

-12.00 Dt ~ +6.00 Dt

From -12.00 to -6.50 (0.50 step)

From -6.00 to +6.00 (0.25 step)